

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250957

Luminaire Tested: **LD8B70D010 ER8B709727 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B709727 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4747.9 lumens
Efficiency: N/A
Efficacy: 62.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBN0H

Luminous Intensity Polar Plot






TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	609.5	12.8
10°-20°	1362.1	28.7
20°-30°	1548.6	32.6
30°-40°	909.5	19.2
40°-50°	244.1	5.1
50°-60°	57.9	1.2
60°-70°	13.2	0.3
70°-80°	2.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3520.2	74.1
0°-40°	4429.6	93.3
0°-60°	4731.6	99.7
0°-90°	4747.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4747.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7248	
5°	6735	609
15°	4872	1362
25°	3417	1549
35°	1416	909
45°	292	244
55°	58	58
65°	13	13
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7247.9
1°	7207.8
2°	7134.0
3°	7029.8
4°	6895.1
5°	6734.7
6°	6553.5
7°	6348.3
8°	6143.0
9°	5936.2
10°	5739.0
11°	5546.5
12°	5365.3
13°	5197.0
14°	5028.6
15°	4871.5
16°	4717.5
17°	4565.2
18°	4417.7
19°	4268.5
20°	4122.6
21°	3976.7
22°	3837.2
23°	3699.3
24°	3558.2
25°	3417.1
26°	3271.2
27°	3112.4
28°	2945.6
29°	2762.8
30°	2565.6
32.5°	2012.4
35°	1415.9
37.5°	933.2
40°	610.9
42.5°	421.7
45°	291.8
47.5°	200.4
50°	133.1
52.5°	86.6
55°	57.7
57.5°	38.5
60°	25.7
62.5°	17.6
65°	12.8



TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	8.0
70°	4.8
72.5°	3.2
75°	3.2
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)