

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251100

Luminaire Tested: **LD8B60D010 ER8B60927 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60927 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5251.6 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251100

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251100

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251100

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	280.3	5.3
10°-20°	793.4	15.1
20°-30°	1181.2	22.5
30°-40°	1341.8	25.6
40°-50°	1096.8	20.9
50°-60°	429.8	8.2
60°-70°	100.1	1.9
70°-80°	24.2	0.5
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2254.9	42.9
0°-40°	3596.8	68.5
0°-60°	5123.4	97.6
0°-90°	5251.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5251.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2978	
5°	2957	280
15°	2813	793
25°	2570	1181
35°	2156	1342
45°	1456	1097
55°	447	430
65°	93	100
75°	22	24
85°	3	4
90°	0	



TEST NUMBER: P251100

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2977.5
2.5°	2972.8
5°	2957.0
7.5°	2930.2
10°	2897.0
12.5°	2855.9
15°	2813.3
17.5°	2762.7
20°	2707.4
22.5°	2642.6
25°	2570.0
27.5°	2484.7
30°	2388.4
32.5°	2279.4
35°	2156.2
37.5°	2020.3
40°	1868.6
42.5°	1685.5
45°	1456.4
47.5°	1187.9
50°	908.2
52.5°	652.4
55°	447.1
57.5°	292.3
60°	195.9
62.5°	134.2
65°	93.1
67.5°	61.6
70°	41.1
72.5°	28.5
75°	22.2
77.5°	15.8
80°	9.5
82.5°	4.7
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)