

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250933

Luminaire Tested: **LD8B70D010 ER8B709727 8LBW0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B709727 8LBW0H
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5255.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250933

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P250933

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	71	77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59	68	62	58	66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250933

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.0	6.3
10°-20°	952.7	18.1
20°-30°	1433.8	27.3
30°-40°	1419.5	27.0
40°-50°	721.3	13.7
50°-60°	290.6	5.5
60°-70°	88.0	1.7
70°-80°	15.2	0.3
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2718.6	51.7
0°-40°	4138.1	78.7
0°-60°	5150.0	98.0
0°-90°	5255.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5255.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3524	
5°	3502	332
15°	3378	953
25°	3132	1434
35°	2336	1420
45°	884	721
55°	313	291
65°	80	88
75°	12	15
85°	2	2
90°	0	



TEST NUMBER: P250933

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3523.7
1°	3516.1
2°	3510.0
3°	3508.5
4°	3507.0
5°	3502.4
6°	3496.3
7°	3484.2
8°	3466.0
9°	3449.3
10°	3431.0
11°	3415.8
12°	3405.2
13°	3397.6
14°	3388.5
15°	3377.9
16°	3364.2
17°	3347.5
18°	3327.8
19°	3305.0
20°	3279.2
21°	3251.8
22°	3224.5
23°	3195.6
24°	3165.2
25°	3131.8
26°	3095.4
27°	3048.3
28°	2993.6
29°	2928.3
30°	2852.4
32.5°	2630.6
35°	2336.0
37.5°	1968.4
40°	1558.3
42.5°	1177.1
45°	884.0
47.5°	675.9
50°	530.1
52.5°	411.6
55°	312.9
57.5°	232.4
60°	174.7
62.5°	124.5
65°	80.5



TEST NUMBER: P250933

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	50.1
70°	31.9
72.5°	19.7
75°	12.2
77.5°	7.6
80°	4.6
82.5°	3.0
85°	1.5
87.5°	0.0
90°	0.0

(END OF REPORT)