

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251125

Luminaire Tested: **LD8B70D010 ER8B709727 8LBW0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251125  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P200903)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B70D010 ER8B709727 8LBW0WH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5413.0 lumens  
Efficiency: N/A  
Efficacy: 71.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.11  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251125

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251125

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78	75	72	70
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61		69	64	61		68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52		61	55	51		59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P251125

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	354.3	6.5
10°-20°	1090.4	20.1
20°-30°	1599.8	29.6
30°-40°	1413.2	26.1
40°-50°	723.9	13.4
50°-60°	202.4	3.7
60°-70°	25.8	0.5
70°-80°	2.7	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3044.5	56.2
0°-40°	4457.7	82.4
0°-60°	5384.0	99.5
0°-90°	5413.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5413.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3546	
5°	3641	354
15°	3879	1090
25°	3528	1600
35°	2273	1413
45°	916	724
55°	206	202
65°	14	26
75°	0	3
85°	0	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251125

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3546.0
2.5°	3559.6
5°	3640.8
7.5°	3752.1
10°	3836.3
12.5°	3877.4
15°	3878.8
17.5°	3839.8
20°	3773.3
22.5°	3668.0
25°	3528.0
27.5°	3319.1
30°	3017.3
32.5°	2659.5
35°	2273.2
37.5°	1896.6
40°	1553.2
42.5°	1229.1
45°	915.7
47.5°	653.6
50°	450.2
52.5°	314.6
55°	206.5
57.5°	131.2
60°	78.2
62.5°	40.6
65°	13.6
67.5°	8.8
70°	7.6
72.5°	4.4
75°	0.0
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251125

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0WH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)