

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251007

Luminaire Tested: **LD8B70D010 ER8B709730 8LBS0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251007  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B70D010 ER8B709730 8LBS0H  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6080.0 lumens  
Efficiency: N/A  
Efficacy: 80.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251007

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBS0H

### Luminous Intensity Polar Plot





TEST NUMBER: P251007

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBS0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56	65	59	55	63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P251007

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBS0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	332.3	5.5
10°-20°	944.8	15.5
20°-30°	1413.3	23.2
30°-40°	1580.8	26.0
40°-50°	1240.1	20.4
50°-60°	452.5	7.4
60°-70°	92.3	1.5
70°-80°	19.8	0.3
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2690.4	44.2
0°-40°	4271.1	70.2
0°-60°	5963.8	98.1
0°-90°	6080.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6080.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3528	
5°	3503	332
15°	3347	945
25°	3078	1413
35°	2544	1581
45°	1642	1240
55°	463	452
65°	84	92
75°	18	20
85°	4	4
90°	0	



TEST NUMBER: P251007

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBS0H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3528.4
2.5°	3523.0
5°	3503.3
7.5°	3474.6
10°	3437.0
12.5°	3393.9
15°	3347.3
17.5°	3295.3
20°	3234.4
22.5°	3162.6
25°	3078.4
27.5°	2974.4
30°	2850.7
32.5°	2705.5
35°	2544.1
37.5°	2363.0
40°	2162.2
42.5°	1923.8
45°	1642.3
47.5°	1324.9
50°	995.0
52.5°	697.4
55°	462.6
57.5°	295.8
60°	190.0
62.5°	125.5
65°	84.3
67.5°	53.8
70°	34.1
72.5°	23.3
75°	17.9
77.5°	12.6
80°	9.0
82.5°	5.4
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)