

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250887

Luminaire Tested: **LD8B70D010 ER8B709730 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B709730 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6252.0 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250887

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P250887

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250887

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBSOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.4	5.3
10°-20°	995.7	15.9
20°-30°	1542.4	24.7
30°-40°	1675.1	26.8
40°-50°	1217.3	19.5
50°-60°	413.7	6.6
60°-70°	65.9	1.1
70°-80°	7.1	0.1
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2871.5	45.9
0°-40°	4546.6	72.7
0°-60°	6177.6	98.8
0°-90°	6252.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6252.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3486	
5°	3488	333
15°	3524	996
25°	3368	1542
35°	2700	1675
45°	1603	1217
55°	421	414
65°	57	66
75°	5	7
85°	2	1
90°	0	



TEST NUMBER: P250887

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3485.8
2.5°	3485.8
5°	3487.6
7.5°	3493.0
10°	3503.8
12.5°	3516.3
15°	3523.5
17.5°	3516.3
20°	3487.6
22.5°	3435.6
25°	3367.5
27.5°	3265.3
30°	3118.2
32.5°	2922.8
35°	2700.4
37.5°	2458.4
40°	2194.8
42.5°	1909.7
45°	1603.1
47.5°	1273.1
50°	945.0
52.5°	647.3
55°	421.4
57.5°	256.4
60°	154.2
62.5°	95.0
65°	57.4
67.5°	32.3
70°	14.3
72.5°	9.0
75°	5.4
77.5°	3.6
80°	3.6
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)