

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250834

Luminaire Tested: **LD8B60D010 ER8B60950 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60950 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5483.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250834

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250834

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	103	102	101	100	100	99	98	97	97	95
2	110	106	102	100	108	104	101	99	101	99	96	96	98	96	94	94	95	94	92	92	91
3	106	100	96	93	104	99	95	92	96	93	91	91	94	92	89	89	92	90	88	88	87
4	102	95	91	87	100	94	90	87	92	89	86	86	90	87	85	85	89	86	84	84	83
5	98	91	86	83	96	90	86	82	88	85	82	82	87	84	81	81	85	83	80	80	79
6	94	87	82	79	93	86	82	78	85	81	78	78	83	80	77	77	82	79	77	77	76
7	91	83	78	75	90	83	78	75	81	77	74	74	80	77	74	74	79	76	74	74	72
8	88	80	75	72	86	79	75	71	78	74	71	71	77	74	71	71	76	73	71	71	70
9	85	77	72	69	84	76	72	69	75	71	68	68	75	71	68	68	74	70	68	68	67
10	82	74	69	66	81	73	69	66	73	69	66	66	72	68	66	66	71	68	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	828359
5°	575338
10°	302756
15°	191557
20°	142353
25°	111915
30°	80574
35°	34580
40°	12052
45°	4623
50°	1070
55°	398
60°	0
65°	540
70°	171
75°	441
80°	657
85°	0



TEST NUMBER: P250834

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1490.1	27.2
10°-20°	1731.3	31.6
20°-30°	1494.2	27.3
30°-40°	648.3	11.8
40°-50°	101.6	1.9
50°-60°	7.3	0.1
60°-70°	4.0	0.1
70°-80°	4.2	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4715.7	86.0
0°-40°	5363.9	97.8
0°-60°	5472.9	99.8
0°-90°	5483.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5483.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26863	
5°	18587	###
15°	6000	1731
25°	3289	1494
35°	919	648
45°	106	102
55°	7	7
65°	7	4
75°	4	4
85°	0	2
90°	0	



TEST NUMBER: P250834

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	26863.1
2.5°	24258.0
5°	18586.8
7.5°	13255.8
10°	9669.0
12.5°	7419.1
15°	6000.4
17.5°	5046.5
20°	4338.0
22.5°	3733.7
25°	3289.3
27.5°	2820.7
30°	2262.9
32.5°	1573.1
35°	918.6
37.5°	513.2
40°	299.4
42.5°	185.9
45°	106.0
47.5°	85.5
50°	22.3
52.5°	11.2
55°	7.4
57.5°	3.7
60°	0.0
62.5°	1.9
65°	7.4
67.5°	5.6
70°	1.9
72.5°	9.3
75°	3.7
77.5°	0.0
80°	3.7
82.5°	1.9
85°	0.0
87.5°	3.7
90°	0.0

(END OF REPORT)