

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246954

Luminaire Tested: **LD8B80D010 ER8B80830 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80830 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8272.0 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246954

CATALOG NUMBER: LD8B80D010 ER8B80830 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P246954

CATALOG NUMBER: LD8B80D010 ER8B80830 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64	60	57	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	418591
5°	401140
10°	353716
15°	298094
20°	244753
25°	198378
30°	146860
35°	88400
40°	39368
45°	15307
50°	5488
55°	1602
60°	1129
65°	839
70°	90
75°	453
80°	0
85°	1344



TEST NUMBER: P246954

CATALOG NUMBER: LD8B80D010 ER8B80830 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1183.1	14.3
10°-20°	2593.5	31.4
20°-30°	2645.0	32.0
30°-40°	1481.4	17.9
40°-50°	315.9	3.8
50°-60°	39.1	0.5
60°-70°	10.2	0.1
70°-80°	2.4	0.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6421.6	77.6
0°-40°	7903.0	95.5
0°-60°	8258.1	99.8
0°-90°	8272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8272.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13575	
5°	12959	###
15°	9338	2594
25°	5830	2645
35°	2348	1481
45°	351	316
55°	30	39
65°	12	10
75°	4	2
85°	4	1
90°	0	



TEST NUMBER: P246954

CATALOG NUMBER: LD8B80D010 ER8B80830 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13574.6
2.5°	13421.7
5°	12959.2
7.5°	12214.8
10°	11296.5
12.5°	10310.8
15°	9337.6
17.5°	8358.6
20°	7458.5
22.5°	6620.9
25°	5830.5
27.5°	5000.6
30°	4124.5
32.5°	3209.0
35°	2348.3
37.5°	1573.3
40°	978.0
42.5°	584.7
45°	351.0
47.5°	195.2
50°	114.4
52.5°	60.6
55°	29.8
57.5°	21.2
60°	18.3
62.5°	8.7
65°	11.5
67.5°	11.5
70°	1.0
72.5°	2.9
75°	3.8
77.5°	1.9
80°	0.0
82.5°	1.0
85°	3.8
87.5°	0.0
90°	0.0

(END OF REPORT)