

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251302

Luminaire Tested: **LD8B60D010 ER8B60950 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60950 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5697.1 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251302

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251302

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100838
5°	100533
10°	99541
15°	98518
20°	97488
25°	95890
30°	93268
35°	89017
40°	82766
45°	69884
50°	47445
55°	24784
60°	11120
65°	5429
70°	2182
75°	1334
80°	994
85°	672



TEST NUMBER: P251302

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.8	5.4
10°-20°	870.5	15.3
20°-30°	1295.8	22.7
30°-40°	1473.0	25.9
40°-50°	1204.5	21.1
50°-60°	448.9	7.9
60°-70°	82.1	1.4
70°-80°	12.7	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2474.0	43.4
0°-40°	3947.0	69.3
0°-60°	5600.4	98.3
0°-90°	5697.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5697.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3270	
5°	3248	308
15°	3086	870
25°	2818	1296
35°	2365	1473
45°	1602	1204
55°	461	449
65°	74	82
75°	11	13
85°	2	2
90°	0	



TEST NUMBER: P251302

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3270.1
2.5°	3264.5
5°	3247.8
7.5°	3218.0
10°	3179.0
12.5°	3134.4
15°	3086.0
17.5°	3030.3
20°	2970.8
22.5°	2900.1
25°	2818.3
27.5°	2725.4
30°	2619.4
32.5°	2498.6
35°	2364.7
37.5°	2221.6
40°	2056.1
42.5°	1851.6
45°	1602.5
47.5°	1303.2
50°	989.0
52.5°	697.1
55°	461.0
57.5°	290.0
60°	180.3
62.5°	115.3
65°	74.4
67.5°	42.8
70°	24.2
72.5°	14.9
75°	11.2
77.5°	7.4
80°	5.6
82.5°	1.9
85°	1.9
87.5°	0.0
90°	0.0

(END OF REPORT)