

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251236

Luminaire Tested: **LD8B60D010 ER8B60950 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60950 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5150.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251236

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251236

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92					92			
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84					84			
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76					76			
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70					70			
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64					64			
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58					58			
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54					54			
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49					49			
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46					46			
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43					43			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123657
5°	120733
10°	116947
15°	115256
20°	113899
25°	111453
30°	104392
35°	85242
40°	50889
45°	30566
50°	22029
55°	14994
60°	9399
65°	4611
70°	1172
75°	441
80°	337
85°	0



TEST NUMBER: P251236

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.9	7.1
10°-20°	1018.9	19.8
20°-30°	1496.2	29.1
30°-40°	1356.4	26.3
40°-50°	580.6	11.3
50°-60°	256.9	5.0
60°-70°	68.5	1.3
70°-80°	5.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2882.0	56.0
0°-40°	4238.4	82.3
0°-60°	5075.9	98.6
0°-90°	5150.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5150.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4010	
5°	3900	367
15°	3610	1019
25°	3276	1496
35°	2264	1356
45°	701	581
55°	279	257
65°	63	69
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P251236

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4010.1
2.5°	3978.4
5°	3900.4
7.5°	3811.1
10°	3734.9
12.5°	3671.7
15°	3610.3
17.5°	3545.3
20°	3470.9
22.5°	3383.5
25°	3275.7
27.5°	3130.7
30°	2931.8
32.5°	2652.9
35°	2264.4
37.5°	1755.0
40°	1264.2
42.5°	912.8
45°	700.9
47.5°	565.2
50°	459.2
52.5°	364.4
55°	278.9
57.5°	208.2
60°	152.4
62.5°	106.0
65°	63.2
67.5°	27.9
70°	13.0
72.5°	7.4
75°	3.7
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)