

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251026

Luminaire Tested: **LD8B60D010 ER8B60950 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251026
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60950 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5595.0 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251026

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251026

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125032
5°	122519
10°	118638
15°	117040
20°	116340
25°	114872
30°	108697
35°	89650
40°	55977
45°	35995
50°	27915
55°	21488
60°	16282
65°	10580
70°	4526
75°	2216
80°	994
85°	672



TEST NUMBER: P251026

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	372.3	6.7
10°-20°	1035.7	18.5
20°-30°	1542.7	27.6
30°-40°	1432.7	25.6
40°-50°	676.7	12.1
50°-60°	363.6	6.5
60°-70°	146.0	2.6
70°-80°	23.0	0.4
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2950.8	52.7
0°-40°	4383.5	78.3
0°-60°	5423.7	96.9
0°-90°	5595.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5595.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4055	
5°	3958	372
15°	3666	1036
25°	3376	1543
35°	2382	1433
45°	825	677
55°	400	364
65°	145	146
75°	19	23
85°	2	2
90°	0	



TEST NUMBER: P251026

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4054.7
2.5°	4026.8
5°	3958.1
7.5°	3870.7
10°	3788.9
12.5°	3721.9
15°	3666.2
17.5°	3608.5
20°	3545.3
22.5°	3472.8
25°	3376.2
27.5°	3240.4
30°	3052.7
32.5°	2777.5
35°	2381.5
37.5°	1875.8
40°	1390.6
42.5°	1035.5
45°	825.4
47.5°	689.7
50°	581.9
52.5°	485.2
55°	399.7
57.5°	325.3
60°	264.0
62.5°	206.4
65°	145.0
67.5°	85.5
70°	50.2
72.5°	29.7
75°	18.6
77.5°	11.2
80°	5.6
82.5°	3.7
85°	1.9
87.5°	0.0
90°	0.0

(END OF REPORT)