

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251150

Luminaire Tested: **LD8B60D010 ER8B609730 8LBN0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13946)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B609730 8LBN0WH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4286.0 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.66
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251150

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251150

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89		92	90	87		90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78		84	81	78		83	80	77	76
6	92	84	79	75	90	83	78	74	82	77	74		80	76	74		79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70		77	73	70		76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67		73	69	66		72	69	66	65
9	81	72	67	64	80	72	67	64	71	66	63		70	66	63		69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60		67	63	60		67	63	60	59

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251150

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	752.5	17.6
10°-20°	1458.1	34.0
20°-30°	1312.8	30.6
30°-40°	649.5	15.2
40°-50°	98.8	2.3
50°-60°	4.1	0.1
60°-70°	5.2	0.1
70°-80°	2.0	0.0
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3523.4	82.2
0°-40°	4172.9	97.4
0°-60°	4275.7	99.8
0°-90°	4286.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4286.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8616	
5°	8300	752
15°	5224	1458
25°	2903	1313
35°	1051	649
45°	109	99
55°	2	4
65°	3	5
75°	3	2
85°	4	3
90°	0	



TEST NUMBER: P251150

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	8615.9
1°	8598.0
2°	8602.4
3°	8559.0
4°	8479.8
5°	8300.3
6°	8162.7
7°	7944.4
8°	7651.3
9°	7346.2
10°	6978.2
11°	6649.2
12°	6296.3
13°	5905.9
14°	5569.4
15°	5224.0
16°	4929.3
17°	4669.1
18°	4349.1
19°	4114.2
20°	3884.0
21°	3644.6
22°	3469.7
23°	3266.3
24°	3079.3
25°	2902.9
26°	2695.0
27°	2508.1
28°	2340.5
29°	2156.6
30°	1891.9
31°	1742.3
32°	1553.9
33°	1347.5
34°	1190.4
35°	1051.3
37.5°	665.5
40°	300.6
42.5°	204.9
45°	109.2
47.5°	61.3
50°	1.5
52.5°	6.0
55°	1.5
57.5°	9.0



TEST NUMBER: P251150

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0WH

CANDELA DISTRIBUTION (continued):

	0°
60°	1.5
62.5°	7.5
65°	3.0
67.5°	7.5
70°	4.5
72.5°	1.5
75°	3.0
77.5°	0.0
80°	1.5
82.5°	6.0
85°	4.5
87.5°	0.0
90°	0.0

(END OF REPORT)