

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246962

Luminaire Tested: **LD8B80D010 ER8B80840 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80840 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8546.0 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246962

CATALOG NUMBER: LD8B80D010 ER8B80840 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P246962

CATALOG NUMBER: LD8B80D010 ER8B80840 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64	60	57	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	432458
5°	414426
10°	365433
15°	307969
20°	252862
25°	204948
30°	151724
35°	91329
40°	40673
45°	15813
50°	5670
55°	1656
60°	1166
65°	868
70°	90
75°	477
80°	0
85°	1415



TEST NUMBER: P246962

CATALOG NUMBER: LD8B80D010 ER8B80840 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1222.3	14.3
10°-20°	2679.4	31.4
20°-30°	2732.6	32.0
30°-40°	1530.4	17.9
40°-50°	326.4	3.8
50°-60°	40.4	0.5
60°-70°	10.5	0.1
70°-80°	2.5	0.0
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6634.4	77.6
0°-40°	8164.8	95.5
0°-60°	8531.6	99.8
0°-90°	8546.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8546.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14024	
5°	13388	###
15°	9647	2679
25°	6024	2733
35°	2426	1530
45°	363	326
55°	31	40
65°	12	11
75°	4	3
85°	4	1
90°	0	



TEST NUMBER: P246962

CATALOG NUMBER: LD8B80D010 ER8B80840 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	14024.3
2.5°	13866.3
5°	13388.4
7.5°	12619.5
10°	11670.7
12.5°	10652.3
15°	9646.9
17.5°	8635.5
20°	7705.6
22.5°	6840.3
25°	6023.6
27.5°	5166.2
30°	4261.1
32.5°	3315.3
35°	2426.1
37.5°	1625.4
40°	1010.4
42.5°	604.0
45°	362.6
47.5°	201.7
50°	118.2
52.5°	62.6
55°	30.8
57.5°	21.9
60°	18.9
62.5°	8.9
65°	11.9
67.5°	11.9
70°	1.0
72.5°	3.0
75°	4.0
77.5°	2.0
80°	0.0
82.5°	1.0
85°	4.0
87.5°	0.0
90°	0.0

(END OF REPORT)