

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251033

Luminaire Tested: **LD8B70D010 ER8B70827 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70827 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6207.0 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251033

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251033

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	278742
5°	274857
10°	251489
15°	215922
20°	181820
25°	150189
30°	112681
35°	67161
40°	31990
45°	13937
50°	6289
55°	2763
60°	1640
65°	897
70°	929
75°	0
80°	355
85°	1486



TEST NUMBER: P251033

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	820.0	13.2
10°-20°	1884.6	30.4
20°-30°	1999.6	32.2
30°-40°	1141.0	18.4
40°-50°	282.8	4.6
50°-60°	55.5	0.9
60°-70°	16.7	0.3
70°-80°	3.7	0.1
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4704.3	75.8
0°-40°	5845.2	94.2
0°-60°	6183.5	99.6
0°-90°	6207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9039	
5°	8880	820
15°	6764	1885
25°	4414	2000
35°	1784	1141
45°	320	283
55°	51	56
65°	12	17
75°	0	4
85°	4	3
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251033

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	9039.4
2.5°	9035.2
5°	8879.5
7.5°	8537.4
10°	8031.7
12.5°	7421.1
15°	6763.6
17.5°	6136.9
20°	5540.7
22.5°	4967.4
25°	4414.2
27.5°	3820.1
30°	3164.6
32.5°	2459.9
35°	1784.1
37.5°	1229.1
40°	794.7
42.5°	503.9
45°	319.6
47.5°	209.1
50°	131.1
52.5°	79.7
55°	51.4
57.5°	41.1
60°	26.6
62.5°	24.6
65°	12.3
67.5°	12.3
70°	10.3
72.5°	6.0
75°	0.0
77.5°	2.0
80°	2.0
82.5°	4.2
85°	4.2
87.5°	2.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251033

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)