

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251285

Luminaire Tested: **LD8B70D010 ER8B70827 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70827 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6996.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251285

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251285

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123829
5°	123454
10°	122236
15°	120983
20°	119714
25°	117754
30°	114536
35°	109315
40°	101637
45°	85818
50°	58263
55°	30440
60°	13654
65°	6662
70°	2678
75°	1632
80°	1208
85°	814



TEST NUMBER: P251285

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.0	5.4
10°-20°	1068.9	15.3
20°-30°	1591.2	22.7
30°-40°	1808.8	25.9
40°-50°	1479.1	21.1
50°-60°	551.3	7.9
60°-70°	100.8	1.4
70°-80°	15.6	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3038.1	43.4
0°-40°	4847.0	69.3
0°-60°	6877.4	98.3
0°-90°	6996.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6996.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4016	
5°	3988	378
15°	3790	1069
25°	3461	1591
35°	2904	1809
45°	1968	1479
55°	566	551
65°	91	101
75°	14	16
85°	2	2
90°	0	



TEST NUMBER: P251285

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4015.7
2.5°	4008.8
5°	3988.3
7.5°	3951.8
10°	3903.8
12.5°	3849.0
15°	3789.7
17.5°	3721.2
20°	3648.1
22.5°	3561.4
25°	3460.9
27.5°	3346.8
30°	3216.7
32.5°	3068.3
35°	2903.9
37.5°	2728.1
40°	2524.9
42.5°	2273.8
45°	1967.9
47.5°	1600.3
50°	1214.5
52.5°	856.1
55°	566.2
57.5°	356.1
60°	221.4
62.5°	141.5
65°	91.3
67.5°	52.5
70°	29.7
72.5°	18.3
75°	13.7
77.5°	9.1
80°	6.8
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0

(END OF REPORT)