

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251329

Luminaire Tested: **LD8B70D010 ER8B70827 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251329
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70827 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4496.0 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251329

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P251329

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	101	99	98	98	97	96	95	95	93
2	107	102	98	95	105	101	97	94	97	94	92	92	94	92	90	90	92	90	88	88	86
3	102	95	90	86	100	94	89	85	91	87	84	84	89	85	82	82	86	84	81	81	80
4	96	88	83	78	94	87	82	78	85	80	77	77	83	79	76	76	81	78	75	75	74
5	91	82	76	72	89	81	76	71	80	75	71	71	78	74	70	70	76	73	70	70	68
6	86	77	71	66	85	76	70	66	74	69	65	65	73	68	65	65	72	68	65	65	63
7	82	72	66	61	80	71	65	61	70	64	61	61	69	64	60	60	67	63	60	60	58
8	77	67	61	57	76	67	61	57	66	60	56	56	65	60	56	56	64	59	56	56	54
9	73	63	57	53	72	63	57	53	62	56	52	52	61	56	52	52	60	55	52	52	51
10	70	59	53	49	68	59	53	49	58	53	49	49	57	52	49	49	57	52	49	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126780
5°	123590
10°	120301
15°	118062
20°	114991
25°	110915
30°	101768
35°	78029
40°	37126
45°	14138
50°	6898
55°	2822
60°	703
65°	168
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251329

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.4	8.4
10°-20°	1040.7	23.1
20°-30°	1486.0	33.1
30°-40°	1231.5	27.4
40°-50°	303.7	6.8
50°-60°	54.6	1.2
60°-70°	3.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2903.1	64.6
0°-40°	4134.6	92.0
0°-60°	4493.0	99.9
0°-90°	4496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4111	
5°	3993	376
15°	3698	1041
25°	3260	1486
35°	2073	1232
45°	324	304
55°	52	55
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P251329

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBW0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4111.4
2.5°	4077.1
5°	3992.7
7.5°	3910.5
10°	3842.0
12.5°	3775.8
15°	3698.2
17.5°	3606.9
20°	3504.2
22.5°	3387.7
25°	3259.9
27.5°	3086.4
30°	2858.1
32.5°	2536.2
35°	2072.8
37.5°	1497.5
40°	922.3
42.5°	536.5
45°	324.2
47.5°	214.6
50°	143.8
52.5°	93.6
55°	52.5
57.5°	25.1
60°	11.4
62.5°	4.6
65°	2.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)