

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251219

Luminaire Tested: **LD8B70D010 ER8B70827 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70827 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6325.0 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251219

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251219

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151869
5°	148279
10°	143628
15°	141555
20°	139885
25°	136882
30°	128209
35°	104688
40°	62498
45°	37539
50°	27057
55°	18413
60°	11545
65°	5662
70°	1443
75°	548
80°	408
85°	0



TEST NUMBER: P251219

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	450.7	7.1
10°-20°	1251.3	19.8
20°-30°	1837.6	29.1
30°-40°	1665.8	26.3
40°-50°	713.1	11.3
50°-60°	315.5	5.0
60°-70°	84.1	1.3
70°-80°	6.6	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3539.6	56.0
0°-40°	5205.4	82.3
0°-60°	6234.0	98.6
0°-90°	6325.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6325.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4925	
5°	4790	451
15°	4434	1251
25°	4023	1838
35°	2781	1666
45°	861	713
55°	342	316
65°	78	84
75°	5	7
85°	0	0
90°	0	



TEST NUMBER: P251219

CATALOG NUMBER: LD8B70D010 ER8B70827 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4925.0
2.5°	4886.2
5°	4790.3
7.5°	4680.7
10°	4587.0
12.5°	4509.4
15°	4434.1
17.5°	4354.2
20°	4262.8
22.5°	4155.5
25°	4023.1
27.5°	3845.0
30°	3600.7
32.5°	3258.2
35°	2781.0
37.5°	2155.4
40°	1552.6
42.5°	1121.1
45°	860.8
47.5°	694.1
50°	564.0
52.5°	447.5
55°	342.5
57.5°	255.7
60°	187.2
62.5°	130.1
65°	77.6
67.5°	34.2
70°	16.0
72.5°	9.1
75°	4.6
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)