

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251397

Luminaire Tested: **LD8B70D010 ER8B70830 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251397
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70830 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6598.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251397

CATALOG NUMBER: LD8B70D010 ER8B70830 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P251397

CATALOG NUMBER: LD8B70D010 ER8B70830 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56		65	60	55		64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117863
5°	117734
10°	117116
15°	116268
20°	114982
25°	113164
30°	109843
35°	104673
40°	96952
45°	81353
50°	53782
55°	26553
60°	10540
65°	4101
70°	631
75°	0
80°	0
85°	0



TEST NUMBER: P251397

CATALOG NUMBER: LD8B70D010 ER8B70830 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.0	5.5
10°-20°	1026.6	15.6
20°-30°	1528.0	23.2
30°-40°	1730.6	26.2
40°-50°	1399.2	21.2
50°-60°	485.3	7.4
60°-70°	66.4	1.0
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2915.6	44.2
0°-40°	4646.2	70.4
0°-60°	6530.7	99.0
0°-90°	6598.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6598.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3822	
5°	3804	361
15°	3642	1027
25°	3326	1528
35°	2781	1731
45°	1866	1399
55°	494	485
65°	56	66
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P251397

CATALOG NUMBER: LD8B70D010 ER8B70830 8LBS0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3822.2
2.5°	3817.5
5°	3803.5
7.5°	3775.4
10°	3740.3
12.5°	3693.5
15°	3642.0
17.5°	3576.4
20°	3503.9
22.5°	3419.6
25°	3326.0
27.5°	3213.6
30°	3084.9
32.5°	2939.8
35°	2780.6
37.5°	2605.1
40°	2408.5
42.5°	2167.4
45°	1865.5
47.5°	1500.3
50°	1121.1
52.5°	767.7
55°	493.9
57.5°	292.6
60°	170.9
62.5°	100.6
65°	56.2
67.5°	25.7
70°	7.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)