

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249938

Luminaire Tested: **LD8B80D010 ER8B80927 8LBM0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13954)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80927 8LBM0H
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6374.3 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249938

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P249938

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91	89	87	86
3	101	95	90	85	99	93	89	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	76		83	79	76		81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		71	67	64	63
7	81	72	65	61	80	71	65	61	70	64	60		68	64	60		67	63	60	58
8	77	67	61	57	76	67	61	56	65	60	56		64	60	56		63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	53		61	56	52		60	55	52	51
10	70	60	53	49	69	59	53	49	58	53	49		57	53	49		57	52	49	48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P249938

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	608.2	9.5
10°-20°	1530.3	24.0
20°-30°	1986.7	31.2
30°-40°	1499.5	23.5
40°-50°	548.7	8.6
50°-60°	153.4	2.4
60°-70°	40.4	0.6
70°-80°	6.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4125.3	64.7
0°-40°	5624.8	88.2
0°-60°	6326.9	99.3
0°-90°	6374.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6374.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6672	
5°	6548	608
15°	5439	1530
25°	4392	1987
35°	2422	1500
45°	658	549
55°	157	153
65°	38	40
75°	6	7
85°	0	0
90°	0	



TEST NUMBER: P249938

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBM0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6671.8
1°	6681.7
2°	6673.8
3°	6648.0
4°	6604.2
5°	6548.5
6°	6467.1
7°	6377.6
8°	6274.2
9°	6160.8
10°	6041.6
11°	5922.3
12°	5799.0
13°	5673.8
14°	5554.6
15°	5439.3
16°	5329.9
17°	5224.5
18°	5129.1
19°	5029.7
20°	4928.3
22.5°	4675.8
25°	4391.6
27.5°	4015.8
30°	3558.6
32.5°	3007.9
35°	2421.5
37.5°	1848.8
40°	1333.9
42.5°	944.3
45°	658.0
47.5°	463.2
50°	312.1
52.5°	228.6
55°	157.0
57.5°	113.3
60°	75.6
62.5°	55.7
65°	37.8
67.5°	25.9
70°	14.0
72.5°	9.9
75°	6.0
77.5°	2.0
80°	2.0



TEST NUMBER: P249938

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBM0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)