

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251039

Luminaire Tested: **LD8B70D010 ER8B70840 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251039  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B70D010 ER8B70840 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 4000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6573.0 lumens  
Efficiency: N/A  
Efficacy: 86.6 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251039

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P251039

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	59		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	295181
5°	291065
10°	266318
15°	228653
20°	192544
25°	159046
30°	119325
35°	71121
40°	33874
45°	14762
50°	6659
55°	2925
60°	1733
65°	949
70°	983
75°	0
80°	373
85°	1592



TEST NUMBER: P251039

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	868.4	13.2
10°-20°	1995.8	30.4
20°-30°	2117.5	32.2
30°-40°	1208.2	18.4
40°-50°	299.5	4.6
50°-60°	58.7	0.9
60°-70°	17.6	0.3
70°-80°	3.9	0.1
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4981.6	75.8
0°-40°	6189.9	94.2
0°-60°	6548.1	99.6
0°-90°	6573.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6573.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9572	
5°	9403	868
15°	7162	1996
25°	4674	2117
35°	1889	1208
45°	338	299
55°	54	59
65°	13	18
75°	0	4
85°	4	3
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251039

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9572.5
2.5°	9568.0
5°	9403.1
7.5°	9040.8
10°	8505.3
12.5°	7858.7
15°	7162.4
17.5°	6498.7
20°	5867.5
22.5°	5260.3
25°	4674.5
27.5°	4045.3
30°	3351.2
32.5°	2605.0
35°	1889.3
37.5°	1301.5
40°	841.5
42.5°	533.6
45°	338.5
47.5°	221.4
50°	138.8
52.5°	84.4
55°	54.4
57.5°	43.5
60°	28.1
62.5°	26.0
65°	13.0
67.5°	13.0
70°	10.9
72.5°	6.4
75°	0.0
77.5°	2.1
80°	2.1
82.5°	4.5
85°	4.5
87.5°	2.1
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251039

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)