

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250365

Luminaire Tested: **LD8B80D010 ER8B80930 8LBN0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250365  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B80D010 ER8B80930 8LBN0GPH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5602.7 lumens  
Efficiency: N/A  
Efficacy: 75.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250365

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250365

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250365

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	803.7	14.3
10°-20°	1746.8	31.2
20°-30°	1875.3	33.5
30°-40°	1013.5	18.1
40°-50°	158.1	2.8
50°-60°	4.3	0.1
60°-70°	1.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4425.7	79.0
0°-40°	5439.2	97.1
0°-60°	5601.6	100.0
0°-90°	5602.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5602.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8953	
5°	8776	804
15°	6237	1747
25°	4157	1875
35°	1592	1014
45°	146	158
55°	0	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250365

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8952.6
1°	8969.7
2°	8961.3
3°	8930.6
4°	8871.6
5°	8776.1
6°	8644.6
7°	8467.8
8°	8246.4
9°	7991.6
10°	7708.2
11°	7411.0
12°	7102.8
13°	6794.7
14°	6508.5
15°	6236.7
16°	5987.1
17°	5746.1
18°	5521.8
19°	5311.9
20°	5109.9
21°	4913.6
22°	4728.5
23°	4543.7
24°	4350.4
25°	4156.8
26°	3960.5
27°	3736.4
28°	3489.7
29°	3237.7
30°	2974.0
31°	2691.0
32°	2407.7
33°	2127.4
34°	1844.4
35°	1592.0
37.5°	1017.4
40°	588.6
42.5°	314.0
45°	145.8
47.5°	78.7
50°	25.4
52.5°	2.8
55°	0.0
57.5°	2.8



TEST NUMBER: P250365

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	2.8
62.5°	0.0
65°	0.0
67.5°	2.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)