

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247042

Luminaire Tested: **LD8B80D010 ER8B80930 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80930 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6580.3 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247042

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247042

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		98	95	94		95	93	92	90
3	105	100	95	92	103	98	94	91	96	92	90		93	91	88		91	89	87	85
4	101	94	90	86	99	93	89	85	91	87	84		89	86	83		87	85	83	81
5	97	90	85	81	95	89	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	80	76	83	79	76		82	78	75		80	77	75	73
7	89	81	76	72	88	81	76	72	79	75	72		78	74	72		77	74	71	70
8	86	78	72	69	85	77	72	69	76	72	69		75	71	68		74	71	68	67
9	82	74	69	66	81	74	69	66	73	69	65		72	68	65		71	68	65	64
10	79	71	66	63	79	71	66	63	70	66	63		69	65	62		69	65	62	61

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247042

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1371.0	20.8
10°-20°	2267.3	34.5
20°-30°	1911.4	29.0
30°-40°	867.4	13.2
40°-50°	151.4	2.3
50°-60°	8.2	0.1
60°-70°	1.2	0.0
70°-80°	1.4	0.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5549.7	84.3
0°-40°	6417.1	97.5
0°-60°	6576.7	99.9
0°-90°	6580.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6580.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16716	
5°	15767	###
15°	8003	2267
25°	4213	1911
35°	1333	867
45°	164	151
55°	7	8
65°	2	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P247042

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	16716.5
2.5°	16568.6
5°	15766.8
7.5°	14020.2
10°	11738.6
12.5°	9629.5
15°	8002.7
17.5°	6780.6
20°	5803.6
22.5°	4943.9
25°	4213.2
27.5°	3469.9
30°	2692.1
32.5°	1959.6
35°	1332.9
37.5°	818.3
40°	481.5
42.5°	282.4
45°	164.3
47.5°	98.3
50°	38.0
52.5°	5.8
55°	6.6
57.5°	5.8
60°	0.8
62.5°	0.8
65°	2.5
67.5°	0.0
70°	2.5
72.5°	4.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.8
87.5°	2.5
90°	0.0

(END OF REPORT)