

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247090

Luminaire Tested: **LD8B80D010 ER8B80930 8LBWOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80930 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7361.6 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247090

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247090

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92				
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68				
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62				
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51				
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47				
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43				
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247090

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.5	5.5
10°-20°	1260.2	17.1
20°-30°	1992.9	27.1
30°-40°	2047.8	27.8
40°-50°	1270.2	17.3
50°-60°	360.1	4.9
60°-70°	24.3	0.3
70°-80°	3.3	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3655.5	49.7
0°-40°	5703.3	77.5
0°-60°	7333.6	99.6
0°-90°	7361.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7361.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4108	
5°	4172	402
15°	4457	1260
25°	4370	1993
35°	3320	2048
45°	1640	1270
55°	360	360
65°	15	24
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P247090

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4107.9
2.5°	4115.9
5°	4172.1
7.5°	4238.3
10°	4301.4
12.5°	4379.3
15°	4457.3
17.5°	4501.6
20°	4498.7
22.5°	4455.3
25°	4370.4
27.5°	4216.5
30°	3978.8
32.5°	3665.9
35°	3319.5
37.5°	2927.8
40°	2502.5
42.5°	2060.4
45°	1640.0
47.5°	1249.2
50°	896.0
52.5°	603.0
55°	360.2
57.5°	185.5
60°	80.9
62.5°	32.6
65°	14.8
67.5°	8.9
70°	5.9
72.5°	4.0
75°	3.0
77.5°	2.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)