

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250337

Luminaire Tested: **LD8B80D010 ER8B80935 8LBN0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250337  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B80D010 ER8B80935 8LBN0GPH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 3500 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5785.9 lumens  
Efficiency: N/A  
Efficacy: 77.8 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250337

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250337

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	285097
5°	280540
10°	249253
15°	205614
20°	173166
25°	146055
30°	109359
35°	61891
40°	24470
45°	6572
50°	1257
55°	0
60°	179
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250337

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	830.0	14.3
10°-20°	1803.9	31.2
20°-30°	1936.6	33.5
30°-40°	1046.7	18.1
40°-50°	163.3	2.8
50°-60°	4.4	0.1
60°-70°	1.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4570.4	79.0
0°-40°	5617.1	97.1
0°-60°	5784.9	100.0
0°-90°	5785.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5785.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9246	
5°	9063	830
15°	6441	1804
25°	4293	1937
35°	1644	1047
45°	151	163
55°	0	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250337

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9245.5
1°	9263.0
2°	9254.3
3°	9222.6
4°	9161.7
5°	9063.1
6°	8927.3
7°	8744.7
8°	8516.1
9°	8252.9
10°	7960.3
11°	7653.4
12°	7335.0
13°	7016.9
14°	6721.3
15°	6440.7
16°	6183.0
17°	5934.0
18°	5702.4
19°	5485.6
20°	5277.0
21°	5074.3
22°	4883.1
23°	4692.4
24°	4492.6
25°	4292.7
26°	4090.1
27°	3858.6
28°	3603.8
29°	3343.6
30°	3071.3
31°	2779.0
32°	2486.4
33°	2197.0
34°	1904.7
35°	1644.1
37.5°	1050.7
40°	607.9
42.5°	324.3
45°	150.7
47.5°	81.2
50°	26.2
52.5°	2.9
55°	0.0
57.5°	2.9



TEST NUMBER: P250337

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	2.9
62.5°	0.0
65°	0.0
67.5°	2.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)