

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250957

Luminaire Tested: **LD8B70D010 ER8B70927 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70927 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5341.4 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	685.7	12.8
10°-20°	1532.3	28.7
20°-30°	1742.2	32.6
30°-40°	1023.2	19.2
40°-50°	274.5	5.1
50°-60°	65.1	1.2
60°-70°	14.8	0.3
70°-80°	3.3	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3960.2	74.1
0°-40°	4983.3	93.3
0°-60°	5323.0	99.7
0°-90°	5341.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5341.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8154	
5°	7576	686
15°	5480	1532
25°	3844	1742
35°	1593	1023
45°	328	275
55°	65	65
65°	14	15
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	8153.9
1°	8108.8
2°	8025.8
3°	7908.5
4°	7757.0
5°	7576.5
6°	7372.7
7°	7141.8
8°	6910.9
9°	6678.2
10°	6456.4
11°	6239.8
12°	6036.0
13°	5846.6
14°	5657.2
15°	5480.4
16°	5307.2
17°	5135.8
18°	4969.9
19°	4802.1
20°	4637.9
21°	4473.8
22°	4316.8
23°	4161.7
24°	4003.0
25°	3844.2
26°	3680.1
27°	3501.4
28°	3313.8
29°	3108.2
30°	2886.3
32.5°	2264.0
35°	1592.9
37.5°	1049.9
40°	687.3
42.5°	474.4
45°	328.3
47.5°	225.4
50°	149.7
52.5°	97.4
55°	64.9
57.5°	43.3
60°	28.9
62.5°	19.8
65°	14.4



TEST NUMBER: P250957

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	9.0
70°	5.4
72.5°	3.6
75°	3.6
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)