

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251149

Luminaire Tested: **LD8B70D010 ER8B70927 8LBN0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13946)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70927 8LBN0WH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5501.1 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.66
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251149

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251149

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89		92	90	87		90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78		84	81	78		83	80	77	76
6	92	84	79	75	90	83	78	74	82	77	74		80	76	74		79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70		77	73	70		76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67		73	69	66		72	69	66	65
9	81	72	67	64	80	72	67	64	71	67	63		70	66	63		69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60		67	63	60		67	63	60	59

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251149

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	965.8	17.6
10°-20°	1871.6	34.0
20°-30°	1685.0	30.6
30°-40°	833.7	15.2
40°-50°	126.8	2.3
50°-60°	5.2	0.1
60°-70°	6.7	0.1
70°-80°	2.5	0.0
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4522.4	82.2
0°-40°	5356.1	97.4
0°-60°	5488.1	99.8
0°-90°	5501.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5501.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11059	
5°	10654	966
15°	6705	1872
25°	3726	1685
35°	1349	834
45°	140	127
55°	2	5
65°	4	7
75°	4	2
85°	6	4
90°	0	



TEST NUMBER: P251149

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	11058.9
1°	11035.8
2°	11041.5
3°	10985.8
4°	10884.2
5°	10653.9
6°	10477.2
7°	10197.0
8°	9820.7
9°	9429.1
10°	8956.8
11°	8534.6
12°	8081.6
13°	7580.5
14°	7148.6
15°	6705.1
16°	6327.0
17°	5993.0
18°	5582.2
19°	5280.8
20°	4985.2
21°	4678.1
22°	4453.4
23°	4192.4
24°	3952.5
25°	3725.9
26°	3459.0
27°	3219.2
28°	3004.2
29°	2768.1
30°	2428.3
31°	2236.4
32°	1994.5
33°	1729.6
34°	1528.0
35°	1349.4
37.5°	854.2
40°	385.9
42.5°	263.0
45°	140.1
47.5°	78.6
50°	1.9
52.5°	7.6
55°	1.9
57.5°	11.6



TEST NUMBER: P251149

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0WH

CANDELA DISTRIBUTION (continued):

	0°
60°	1.9
62.5°	9.7
65°	3.8
67.5°	9.7
70°	5.7
72.5°	1.9
75°	3.8
77.5°	0.0
80°	1.9
82.5°	7.6
85°	5.7
87.5°	0.0
90°	0.0

(END OF REPORT)