

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250935

Luminaire Tested: **LD8B70D010 ER8B70930 8LBW0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250935  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B70D010 ER8B70930 8LBW0H  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6232.8 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250935

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0H

### Luminous Intensity Polar Plot





TEST NUMBER: P250935

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71		79	74	71		77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59		68	62	58		66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42		51	46	42		50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250935

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	393.8	6.3
10°-20°	1130.0	18.1
20°-30°	1700.6	27.3
30°-40°	1683.7	27.0
40°-50°	855.5	13.7
50°-60°	344.7	5.5
60°-70°	104.4	1.7
70°-80°	18.0	0.3
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3224.4	51.7
0°-40°	4908.1	78.7
0°-60°	6108.2	98.0
0°-90°	6232.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6232.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4179	
5°	4154	394
15°	4006	1130
25°	3714	1701
35°	2771	1684
45°	1048	855
55°	371	345
65°	96	104
75°	14	18
85°	2	2
90°	0	



TEST NUMBER: P250935

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4179.3
1°	4170.3
2°	4163.1
3°	4161.3
4°	4159.5
5°	4154.1
6°	4146.9
7°	4132.5
8°	4110.8
9°	4091.1
10°	4069.5
11°	4051.4
12°	4038.9
13°	4029.8
14°	4019.0
15°	4006.3
16°	3990.2
17°	3970.4
18°	3946.9
19°	3919.9
20°	3889.3
21°	3856.9
22°	3824.4
23°	3790.2
24°	3754.2
25°	3714.5
26°	3671.3
27°	3615.4
28°	3550.7
29°	3473.2
30°	3383.1
32.5°	3120.1
35°	2770.6
37.5°	2334.7
40°	1848.3
42.5°	1396.1
45°	1048.5
47.5°	801.6
50°	628.7
52.5°	488.2
55°	371.1
57.5°	275.7
60°	207.2
62.5°	147.7
65°	95.5



TEST NUMBER: P250935

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	59.4
70°	37.8
72.5°	23.4
75°	14.5
77.5°	9.0
80°	5.4
82.5°	3.6
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)