

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250815

Luminaire Tested: **LD8B70D010 ER8B70930 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70930 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6560.1 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250815

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250815

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250815

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.5	5.8
10°-20°	1254.0	19.1
20°-30°	1973.1	30.1
30°-40°	1876.8	28.6
40°-50°	865.3	13.2
50°-60°	196.6	3.0
60°-70°	12.9	0.2
70°-80°	2.6	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3605.6	55.0
0°-40°	5482.4	83.6
0°-60°	6544.3	99.8
0°-90°	6560.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6560.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3774	
5°	3871	378
15°	4449	1254
25°	4327	1973
35°	3076	1877
45°	1059	865
55°	190	197
65°	9	13
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P250815

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3774.5
1°	3772.7
2°	3779.9
3°	3801.4
4°	3833.7
5°	3871.4
6°	3918.0
7°	3968.3
8°	4020.4
9°	4081.3
10°	4146.0
11°	4210.6
12°	4278.9
13°	4343.4
14°	4402.6
15°	4449.4
16°	4483.4
17°	4506.8
18°	4517.5
19°	4515.7
20°	4503.2
21°	4481.6
22°	4454.7
23°	4418.8
24°	4377.5
25°	4327.3
26°	4268.1
27°	4192.7
28°	4103.0
29°	3998.8
30°	3878.5
32.5°	3517.8
35°	3076.2
37.5°	2562.9
40°	2003.0
42.5°	1480.7
45°	1058.9
47.5°	750.2
50°	516.9
52.5°	330.2
55°	190.2
57.5°	95.2
60°	41.3
62.5°	16.1
65°	9.0



TEST NUMBER: P250815

CATALOG NUMBER: LD8B70D010 ER8B70930 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	5.4
70°	3.6
72.5°	3.6
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)