

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251477

Luminaire Tested: **LD8B70D010 ER8B70940 8LBM0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251477
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201674)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70940 8LBM0MW
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6720.1 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.93
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251477

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBM0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251477

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBM0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	89
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	76	73	71
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	64	57	52	62	56	52		61	55	51		60	55	51	49
8	71	60	53	48	70	59	53	48	58	52	48		57	51	47		56	51	47	46
9	67	56	49	44	66	56	49	44	54	48	44		54	48	44		53	48	44	42
10	64	53	46	41	63	52	46	41	51	45	41		50	45	41		50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183821
5°	179162
10°	160167
15°	143933
20°	134037
25°	126277
30°	110406
35°	83657
40°	56186
45°	39601
50°	33586
55°	30628
60°	29023
65°	26107
70°	23487
75°	21124
80°	18593
85°	17938



TEST NUMBER: P251477

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBM0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	529.8	7.9
10°-20°	1271.5	18.9
20°-30°	1684.9	25.1
30°-40°	1381.6	20.6
40°-50°	736.0	11.0
50°-60°	518.0	7.7
60°-70°	357.2	5.3
70°-80°	186.0	2.8
80°-90°	55.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3486.1	51.9
0°-40°	4867.8	72.4
0°-60°	6121.8	91.1
0°-90°	6720.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6720.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5961	
5°	5788	530
15°	4509	1271
25°	3711	1685
35°	2222	1382
45°	908	736
55°	570	518
65°	358	357
75°	177	186
85°	51	55
90°	0	



TEST NUMBER: P251477

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBM0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5961.2
1°	5978.1
2°	5970.9
3°	5935.5
4°	5875.0
5°	5788.0
6°	5679.2
7°	5548.6
8°	5408.5
9°	5259.3
10°	5115.2
11°	4977.3
12°	4837.2
13°	4720.4
14°	4609.7
15°	4508.6
16°	4413.3
17°	4325.4
18°	4244.0
19°	4162.6
20°	4084.6
21°	4008.7
22°	3942.5
23°	3874.8
24°	3795.2
25°	3711.4
26°	3616.3
27°	3509.2
28°	3388.4
29°	3254.5
30°	3100.7
31°	2939.5
32°	2770.3
33°	2589.8
34°	2408.5
35°	2222.3
37.5°	1780.7
40°	1395.8
42.5°	1102.3
45°	908.1
47.5°	779.9
50°	700.1
52.5°	630.2
55°	569.7
57.5°	532.7



TEST NUMBER: P251477

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBM0MW

CANDELA DISTRIBUTION (continued):

	0°
60°	470.6
62.5°	410.3
65°	357.8
67.5°	311.2
70°	260.5
72.5°	217.5
75°	177.3
77.5°	128.2
80°	104.7
82.5°	75.8
85°	50.7
87.5°	23.5
90°	0.0

(END OF REPORT)