

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251455

Luminaire Tested: **LD8B70D010 ER8B70940 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70940 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6175.0 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251455

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251455

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199684
5°	198255
10°	180664
15°	154854
20°	137240
25°	122466
30°	98905
35°	68622
40°	43543
45°	32345
50°	27608
55°	24203
60°	21659
65°	19350
70°	16679
75°	15334
80°	14295
85°	12596



TEST NUMBER: P251455

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	590.8	9.6
10°-20°	1366.4	22.1
20°-30°	1624.9	26.3
30°-40°	1148.7	18.6
40°-50°	592.9	9.6
50°-60°	406.5	6.6
60°-70°	263.9	4.3
70°-80°	138.4	2.2
80°-90°	42.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3582.1	58.0
0°-40°	4730.7	76.6
0°-60°	5730.2	92.8
0°-90°	6175.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6175.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6476	
5°	6405	591
15°	4851	1366
25°	3599	1625
35°	1823	1149
45°	742	593
55°	450	407
65°	265	264
75°	129	138
85°	36	40
90°	0	3
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251455

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6475.6
2.5°	6475.6
5°	6404.8
7.5°	6169.3
10°	5769.8
12.5°	5293.4
15°	4850.7
17.5°	4486.5
20°	4182.2
22.5°	3894.3
25°	3599.4
27.5°	3229.3
30°	2777.7
32.5°	2291.8
35°	1822.9
37.5°	1404.5
40°	1081.7
42.5°	870.4
45°	741.7
47.5°	648.2
50°	575.5
52.5°	511.7
55°	450.2
57.5°	396.0
60°	351.2
62.5°	304.3
65°	265.2
67.5°	229.8
70°	185.0
72.5°	158.9
75°	128.7
77.5°	104.5
80°	80.5
82.5°	59.9
85°	35.6
87.5°	20.6
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251455

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)