

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247758

Luminaire Tested: **LD8B80D010 ER8B809727 8LBS0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-88)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B809727 8LBS0MW
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6451.1 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.24
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247758

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBS0MW

Luminous Intensity Polar Plot






TEST NUMBER: P247758

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBS0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		86	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73		80	76	72		78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71	67	63	61
5	83	72	64	59	81	71	64	58	69	62	58		67	61	57		65	60	57	55
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	47		57	51	46		55	50	46	44
8	67	55	48	43	66	55	47	42	53	47	42		52	46	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48	42	38	37
10	60	47	40	36	58	47	40	35	46	40	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247758

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBS0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.0	5.0
10°-20°	911.9	14.1
20°-30°	1341.6	20.8
30°-40°	1515.4	23.5
40°-50°	1276.2	19.8
50°-60°	643.9	10.0
60°-70°	252.2	3.9
70°-80°	142.5	2.2
80°-90°	44.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2576.6	39.9
0°-40°	4092.0	63.4
0°-60°	6012.0	93.2
0°-90°	6451.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6451.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3426	
5°	3404	323
15°	3242	912
25°	2919	1342
35°	2434	1515
45°	1681	1276
55°	695	644
65°	244	252
75°	139	142
85°	40	44
90°	0	



TEST NUMBER: P247758

CATALOG NUMBER: LD8B80D010 ER8B809727 8LBS0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3425.6
2.5°	3422.1
5°	3404.0
7.5°	3380.3
10°	3339.9
12.5°	3289.8
15°	3241.7
17.5°	3168.6
20°	3095.5
22.5°	3016.2
25°	2919.4
27.5°	2810.1
30°	2695.9
32.5°	2567.8
35°	2434.1
37.5°	2280.9
40°	2125.7
42.5°	1914.0
45°	1680.7
47.5°	1413.4
50°	1148.8
52.5°	910.0
55°	694.9
57.5°	523.6
60°	394.1
62.5°	300.8
65°	244.4
67.5°	199.1
70°	161.5
72.5°	156.0
75°	138.6
77.5°	115.6
80°	97.5
82.5°	62.0
85°	39.7
87.5°	12.5
90°	0.0

(END OF REPORT)