

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246994

Luminaire Tested: **LD8B80D010 ER8B809730 8LBM0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246994  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B80D010 ER8B809730 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6336.9 lumens  
Efficiency: N/A  
Efficacy: 85.2 lumens/watt  
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246994

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P246994

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64	60	57	55

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P246994

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	906.3	14.3
10°-20°	1986.9	31.4
20°-30°	2026.3	32.0
30°-40°	1134.8	17.9
40°-50°	242.0	3.8
50°-60°	30.0	0.5
60°-70°	7.8	0.1
70°-80°	1.8	0.0
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4919.5	77.6
0°-40°	6054.3	95.5
0°-60°	6326.3	99.8
0°-90°	6336.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6336.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10399	
5°	9928	906
15°	7153	1987
25°	4467	2026
35°	1799	1135
45°	269	242
55°	23	30
65°	9	8
75°	3	2
85°	3	1
90°	0	



TEST NUMBER: P246994

CATALOG NUMBER: LD8B80D010 ER8B809730 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10399.2
2.5°	10282.1
5°	9927.7
7.5°	9357.5
10°	8654.0
12.5°	7898.9
15°	7153.3
17.5°	6403.4
20°	5713.8
22.5°	5072.2
25°	4466.6
27.5°	3830.8
30°	3159.7
32.5°	2458.4
35°	1799.0
37.5°	1205.2
40°	749.2
42.5°	447.9
45°	268.9
47.5°	149.5
50°	87.7
52.5°	46.4
55°	22.8
57.5°	16.2
60°	14.0
62.5°	6.6
65°	8.8
67.5°	8.8
70°	0.7
72.5°	2.2
75°	2.9
77.5°	1.5
80°	0.0
82.5°	0.7
85°	2.9
87.5°	0.0
90°	0.0

(END OF REPORT)