

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251237

Luminaire Tested: **LD8B70D010 ER8B70950 8LBW0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251237  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B70D010 ER8B70950 8LBW0GPH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6217.0 lumens  
Efficiency: N/A  
Efficacy: 81.9 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251237

CATALOG NUMBER: LD8B70D010 ER8B70950 8LBW0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P251237

CATALOG NUMBER: LD8B70D010 ER8B70950 8LBW0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	149276
5°	145747
10°	141176
15°	139138
20°	137496
25°	134545
30°	126019
35°	102900
40°	61432
45°	36898
50°	26591
55°	18096
60°	11348
65°	5567
70°	1416
75°	536
80°	391
85°	0



TEST NUMBER: P251237

CATALOG NUMBER: LD8B70D010 ER8B70950 8LBW0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	443.0	7.1
10°-20°	1230.0	19.8
20°-30°	1806.2	29.1
30°-40°	1637.4	26.3
40°-50°	700.9	11.3
50°-60°	310.1	5.0
60°-70°	82.7	1.3
70°-80°	6.5	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3479.1	56.0
0°-40°	5116.5	82.3
0°-60°	6127.5	98.6
0°-90°	6217.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6217.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4841	
5°	4708	443
15°	4358	1230
25°	3954	1806
35°	2734	1637
45°	846	701
55°	337	310
65°	76	83
75°	4	6
85°	0	0
90°	0	



TEST NUMBER: P251237

CATALOG NUMBER: LD8B70D010 ER8B70950 8LBW0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4840.9
2.5°	4802.7
5°	4708.5
7.5°	4600.7
10°	4508.7
12.5°	4432.4
15°	4358.4
17.5°	4279.8
20°	4190.0
22.5°	4084.6
25°	3954.4
27.5°	3779.3
30°	3539.2
32.5°	3202.6
35°	2733.5
37.5°	2118.6
40°	1526.1
42.5°	1101.9
45°	846.1
47.5°	682.3
50°	554.3
52.5°	439.9
55°	336.6
57.5°	251.4
60°	184.0
62.5°	127.9
65°	76.3
67.5°	33.7
70°	15.7
72.5°	9.0
75°	4.5
77.5°	2.2
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)