

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250981

Luminaire Tested: **LD8B70D010 ER8B709727 8LBM0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250981  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27951)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B70D010 ER8B709727 8LBM0H  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5167.0 lumens  
Efficiency: N/A  
Efficacy: 68.1 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250981

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBM0H

### Luminous Intensity Polar Plot





TEST NUMBER: P250981

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBM0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75	72	69	67
6	85	76	70	65	84	75	69	65	74	68	64		72	68	64		71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	53	49	58	52	48		57	52	48		56	51	48	47

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250981

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBM0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	476.9	9.2
10°-20°	1200.4	23.2
20°-30°	1601.7	31.0
30°-40°	1234.5	23.9
40°-50°	460.3	8.9
50°-60°	150.5	2.9
60°-70°	34.7	0.7
70°-80°	7.0	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3278.9	63.5
0°-40°	4513.4	87.4
0°-60°	5124.3	99.2
0°-90°	5167.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5167.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5414	
5°	5165	477
15°	4270	1200
25°	3526	1602
35°	2008	1235
45°	559	460
55°	158	151
65°	31	35
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P250981

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBM0H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5414.3
1°	5390.9
2°	5351.4
3°	5300.8
4°	5239.0
5°	5165.0
6°	5081.0
7°	4984.7
8°	4882.3
9°	4776.1
10°	4678.6
11°	4584.8
12°	4497.1
13°	4416.9
14°	4342.8
15°	4270.0
16°	4195.9
17°	4124.3
18°	4050.3
19°	3977.4
20°	3907.1
21°	3834.2
22°	3763.9
23°	3689.8
24°	3612.0
25°	3525.6
26°	3430.6
27°	3325.6
28°	3209.6
29°	3080.0
30°	2938.0
32.5°	2522.0
35°	2008.5
37.5°	1487.5
40°	1053.0
42.5°	754.3
45°	559.2
47.5°	420.9
50°	311.1
52.5°	222.2
55°	158.0
57.5°	108.6
60°	71.6
62.5°	46.9
65°	30.9



TEST NUMBER: P250981

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBM0H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	21.0
70°	13.6
72.5°	8.6
75°	6.2
77.5°	3.7
80°	2.5
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)