

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251239

Luminaire Tested: **LD8B70D010 ER8B709727 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B709727 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4694.0 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251239

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251239

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251239

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.4	7.1
10°-20°	928.7	19.8
20°-30°	1363.7	29.1
30°-40°	1236.3	26.3
40°-50°	529.2	11.3
50°-60°	234.2	5.0
60°-70°	62.4	1.3
70°-80°	4.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2626.8	56.0
0°-40°	3863.1	82.3
0°-60°	4626.4	98.6
0°-90°	4694.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4694.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3655	
5°	3555	334
15°	3291	929
25°	2986	1364
35°	2064	1236
45°	639	529
55°	254	234
65°	58	62
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P251239

CATALOG NUMBER: LD8B70D010 ER8B709727 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3655.0
2.5°	3626.2
5°	3555.0
7.5°	3473.7
10°	3404.2
12.5°	3346.6
15°	3290.7
17.5°	3231.4
20°	3163.6
22.5°	3083.9
25°	2985.7
27.5°	2853.5
30°	2672.2
32.5°	2418.0
35°	2063.9
37.5°	1599.6
40°	1152.2
42.5°	832.0
45°	638.8
47.5°	515.1
50°	418.5
52.5°	332.1
55°	254.2
57.5°	189.8
60°	138.9
62.5°	96.6
65°	57.6
67.5°	25.4
70°	11.9
72.5°	6.8
75°	3.4
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)