

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250983

Luminaire Tested: **LD8B70D010 ER8B709730 8LBM0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27951)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B709730 8LBM0H
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5466.0 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250983

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P250983

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75	72	69	67
6	85	76	70	65	84	75	69	65	74	68	64		72	68	64		71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	53	49	58	52	48		57	52	48		56	51	48	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250983

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	504.5	9.2
10°-20°	1269.8	23.2
20°-30°	1694.3	31.0
30°-40°	1306.0	23.9
40°-50°	486.9	8.9
50°-60°	159.3	2.9
60°-70°	36.7	0.7
70°-80°	7.4	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3468.6	63.5
0°-40°	4774.6	87.4
0°-60°	5420.8	99.2
0°-90°	5466.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5466.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5728	
5°	5464	504
15°	4517	1270
25°	3730	1694
35°	2125	1306
45°	592	487
55°	167	159
65°	33	37
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P250983

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBM0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5727.6
1°	5702.8
2°	5661.0
3°	5607.5
4°	5542.2
5°	5463.9
6°	5375.1
7°	5273.2
8°	5164.8
9°	5052.5
10°	4949.3
11°	4850.1
12°	4757.4
13°	4672.5
14°	4594.1
15°	4517.1
16°	4438.7
17°	4363.0
18°	4284.6
19°	4207.6
20°	4133.1
21°	4056.1
22°	3981.7
23°	3903.3
24°	3821.0
25°	3729.6
26°	3629.1
27°	3518.1
28°	3395.3
29°	3258.2
30°	3108.0
32.5°	2667.9
35°	2124.7
37.5°	1573.6
40°	1113.9
42.5°	797.9
45°	591.6
47.5°	445.3
50°	329.1
52.5°	235.1
55°	167.2
57.5°	114.9
60°	75.7
62.5°	49.6
65°	32.6



TEST NUMBER: P250983

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBM0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	22.2
70°	14.4
72.5°	9.1
75°	6.5
77.5°	3.9
80°	2.6
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

(END OF REPORT)