

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247007

Luminaire Tested: **LD8B90D010 ER8B90835 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B90D010 ER8B90835 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8974.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 86.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247007

CATALOG NUMBER: LD8B90D010 ER8B90835 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247007

CATALOG NUMBER: LD8B90D010 ER8B90835 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		98	95	94		95	93	92	90
3	105	100	95	92	103	98	94	91	96	92	90		93	91	88		91	89	87	85
4	101	94	90	86	99	93	89	85	91	87	84		89	86	83		87	85	83	81
5	97	90	85	81	95	89	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	80	76	83	79	76		82	78	75		80	77	75	73
7	89	81	76	72	88	81	76	72	79	75	72		78	74	72		77	74	71	70
8	86	78	72	69	85	77	72	69	76	72	69		75	71	68		74	71	68	67
9	82	74	69	66	81	74	69	66	73	69	65		72	68	65		71	68	65	64
10	79	71	66	63	79	71	66	63	70	66	63		69	65	62		69	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	702991
5°	665584
10°	501268
15°	348416
20°	259730
25°	195496
30°	130726
35°	68426
40°	26431
45°	9773
50°	2485
55°	484
60°	68
65°	248
70°	307
75°	0
80°	0
85°	389



TEST NUMBER: P247007

CATALOG NUMBER: LD8B90D010 ER8B90835 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1869.7	20.8
10°-20°	3092.1	34.5
20°-30°	2606.8	29.0
30°-40°	1182.9	13.2
40°-50°	206.5	2.3
50°-60°	11.2	0.1
60°-70°	1.7	0.0
70°-80°	1.9	0.0
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7568.6	84.3
0°-40°	8751.4	97.5
0°-60°	8969.2	99.9
0°-90°	8974.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8974.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22798	
5°	21502	###
15°	10914	3092
25°	5746	2607
35°	1818	1183
45°	224	207
55°	9	11
65°	3	2
75°	0	2
85°	1	1
90°	0	



TEST NUMBER: P247007

CATALOG NUMBER: LD8B90D010 ER8B90835 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	22797.5
2.5°	22595.9
5°	21502.3
7.5°	19120.4
10°	16008.8
12.5°	13132.5
15°	10913.9
17.5°	9247.1
20°	7914.9
22.5°	6742.5
25°	5745.8
27.5°	4732.2
30°	3671.4
32.5°	2672.4
35°	1817.7
37.5°	1116.1
40°	656.6
42.5°	385.2
45°	224.1
47.5°	134.0
50°	51.8
52.5°	7.9
55°	9.0
57.5°	7.9
60°	1.1
62.5°	1.1
65°	3.4
67.5°	0.0
70°	3.4
72.5°	5.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.1
87.5°	3.4
90°	0.0

(END OF REPORT)