

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251031

Luminaire Tested: **LD8B70D010 ER8B709730 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B709730 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5395.0 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251031

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251031

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251031

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.0	6.7
10°-20°	998.7	18.5
20°-30°	1487.6	27.6
30°-40°	1381.5	25.6
40°-50°	652.5	12.1
50°-60°	350.6	6.5
60°-70°	140.8	2.6
70°-80°	22.1	0.4
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2845.3	52.7
0°-40°	4226.8	78.3
0°-60°	5229.9	96.9
0°-90°	5395.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5395.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3910	
5°	3817	359
15°	3535	999
25°	3256	1488
35°	2296	1382
45°	796	653
55°	385	351
65°	140	141
75°	18	22
85°	2	2
90°	0	



TEST NUMBER: P251031

CATALOG NUMBER: LD8B70D010 ER8B709730 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3909.8
2.5°	3882.9
5°	3816.6
7.5°	3732.3
10°	3653.4
12.5°	3588.9
15°	3535.1
17.5°	3479.6
20°	3418.6
22.5°	3348.7
25°	3255.5
27.5°	3124.6
30°	2943.5
32.5°	2678.2
35°	2296.4
37.5°	1808.8
40°	1340.9
42.5°	998.5
45°	795.9
47.5°	665.1
50°	561.1
52.5°	467.9
55°	385.4
57.5°	313.7
60°	254.6
62.5°	199.0
65°	139.8
67.5°	82.5
70°	48.4
72.5°	28.7
75°	17.9
77.5°	10.8
80°	5.4
82.5°	3.6
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)