

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250288

Luminaire Tested: **LD8B80D010 ER8B80827 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80827 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6365.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250288

CATALOG NUMBER: LD8B80D010 ER8B80827 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250288

CATALOG NUMBER: LD8B80D010 ER8B80827 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	313624
5°	308612
10°	274196
15°	226189
20°	190496
25°	160672
30°	120301
35°	68083
40°	26922
45°	7226
50°	1386
55°	0
60°	197
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250288

CATALOG NUMBER: LD8B80D010 ER8B80827 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	913.0	14.3
10°-20°	1984.4	31.2
20°-30°	2130.4	33.5
30°-40°	1151.4	18.1
40°-50°	179.7	2.8
50°-60°	4.9	0.1
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5027.8	79.0
0°-40°	6179.2	97.1
0°-60°	6363.8	100.0
0°-90°	6365.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6365.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10171	
5°	9970	913
15°	7085	1984
25°	4722	2130
35°	1809	1151
45°	166	180
55°	0	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250288

CATALOG NUMBER: LD8B80D010 ER8B80827 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10170.6
1°	10189.9
2°	10180.4
3°	10145.5
4°	10078.5
5°	9970.0
6°	9820.7
7°	9619.8
8°	9368.3
9°	9078.8
10°	8756.9
11°	8419.3
12°	8069.0
13°	7719.1
14°	7393.9
15°	7085.2
16°	6801.7
17°	6527.8
18°	6273.1
19°	6034.5
20°	5805.1
21°	5582.1
22°	5371.8
23°	5161.9
24°	4942.2
25°	4722.3
26°	4499.3
27°	4244.8
28°	3964.4
29°	3678.2
30°	3378.6
31°	3057.1
32°	2735.2
33°	2416.9
34°	2095.3
35°	1808.6
37.5°	1155.9
40°	668.8
42.5°	356.8
45°	165.7
47.5°	89.4
50°	28.9
52.5°	3.2
55°	0.0
57.5°	3.2



TEST NUMBER: P250288

CATALOG NUMBER: LD8B80D010 ER8B80827 8LBN0GPH

CANDELA DISTRIBUTION (continued):

	0°
60°	3.2
62.5°	0.0
65°	0.0
67.5°	3.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)