

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247050

Luminaire Tested: **LD8B80D010 ER8B80830 8LBWOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80830 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8573.0 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247050

CATALOG NUMBER: LD8B80D010 ER8B80830 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247050

CATALOG NUMBER: LD8B80D010 ER8B80830 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147518
5°	150397
10°	156848
15°	165708
20°	171919
25°	173169
30°	164980
35°	145525
40°	117312
45°	83289
50°	50055
55°	22553
60°	5816
65°	1255
70°	622
75°	417
80°	213
85°	0



TEST NUMBER: P247050

CATALOG NUMBER: LD8B80D010 ER8B80830 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	468.7	5.5
10°-20°	1467.5	17.1
20°-30°	2320.8	27.1
30°-40°	2384.7	27.8
40°-50°	1479.3	17.3
50°-60°	419.4	4.9
60°-70°	28.3	0.3
70°-80°	3.8	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4257.0	49.7
0°-40°	6641.7	77.5
0°-60°	8540.4	99.6
0°-90°	8573.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8573.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4784	
5°	4859	469
15°	5191	1468
25°	5090	2321
35°	3866	2385
45°	1910	1479
55°	420	419
65°	17	28
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P247050

CATALOG NUMBER: LD8B80D010 ER8B80830 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4783.9
2.5°	4793.1
5°	4858.7
7.5°	4935.6
10°	5009.2
12.5°	5099.9
15°	5190.7
17.5°	5242.4
20°	5239.0
22.5°	5188.4
25°	5089.6
27.5°	4910.3
30°	4633.4
32.5°	4269.1
35°	3865.8
37.5°	3409.6
40°	2914.3
42.5°	2399.4
45°	1909.9
47.5°	1454.9
50°	1043.4
52.5°	702.2
55°	419.5
57.5°	216.1
60°	94.3
62.5°	38.0
65°	17.2
67.5°	10.3
70°	6.9
72.5°	4.6
75°	3.5
77.5°	2.3
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)