

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250554

Luminaire Tested: **LD8B80D010 ER8B80835 8LBM0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250554  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B80D010 ER8B80835 8LBM0B  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5336.0 lumens  
Efficiency: N/A  
Efficacy: 71.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250554

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250554

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	213498
5°	206972
10°	181265
15°	160032
20°	146645
25°	135025
30°	112385
35°	74645
40°	36329
45°	13157
50°	3958
55°	280
60°	0
65°	190
70°	0
75°	0
80°	462
85°	0



TEST NUMBER: P250554

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	608.1	11.4
10°-20°	1412.3	26.5
20°-30°	1791.7	33.6
30°-40°	1227.5	23.0
40°-50°	279.7	5.2
50°-60°	14.0	0.3
60°-70°	0.6	0.0
70°-80°	1.0	0.0
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3812.2	71.4
0°-40°	5039.6	94.4
0°-60°	5333.3	99.9
0°-90°	5336.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5336.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6924	
5°	6686	608
15°	5013	1412
25°	3968	1792
35°	1983	1227
45°	302	280
55°	5	14
65°	3	1
75°	0	1
85°	0	1
90°	0	



TEST NUMBER: P250554

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6923.6
1°	6959.7
2°	6946.8
3°	6895.3
4°	6807.6
5°	6686.4
6°	6539.4
7°	6369.2
8°	6181.0
9°	5979.8
10°	5789.0
11°	5613.7
12°	5425.5
13°	5288.8
14°	5144.4
15°	5012.9
16°	4894.3
17°	4778.2
18°	4669.9
19°	4564.2
20°	4468.8
21°	4370.8
22°	4270.2
23°	4182.6
24°	4084.6
25°	3968.5
26°	3839.6
27°	3690.0
28°	3530.2
29°	3352.2
30°	3156.3
31°	2934.5
32°	2705.0
33°	2465.2
34°	2220.2
35°	1982.9
37.5°	1400.2
40°	902.5
42.5°	531.2
45°	301.7
47.5°	162.5
50°	82.5
52.5°	15.5
55°	5.2
57.5°	2.6



TEST NUMBER: P250554

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	0.0
62.5°	0.0
65°	2.6
67.5°	0.0
70°	0.0
72.5°	2.6
75°	0.0
77.5°	0.0
80°	2.6
82.5°	0.0
85°	0.0
87.5°	2.6
90°	0.0

(END OF REPORT)