

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250470

Luminaire Tested: **LD8B80D010 ER8B80835 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250470
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80835 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7324.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250470

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250470

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	286432
5°	279191
10°	250277
15°	222910
20°	203347
25°	184754
30°	151496
35°	99701
40°	49734
45°	18512
50°	5622
55°	677
60°	395
65°	0
70°	289
75°	1132
80°	0
85°	1132



TEST NUMBER: P250470

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	827.0	11.3
10°-20°	1966.2	26.8
20°-30°	2449.6	33.4
30°-40°	1652.3	22.6
40°-50°	390.7	5.3
50°-60°	28.6	0.4
60°-70°	5.1	0.1
70°-80°	3.8	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5242.7	71.6
0°-40°	6895.0	94.1
0°-60°	7314.3	99.9
0°-90°	7324.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7324.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9289	
5°	9020	827
15°	6982	1966
25°	5430	2450
35°	2648	1652
45°	424	391
55°	13	29
65°	0	5
75°	10	4
85°	3	1
90°	0	



TEST NUMBER: P250470

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9288.8
2.5°	9272.9
5°	9019.5
7.5°	8560.1
10°	7993.0
12.5°	7457.6
15°	6982.5
17.5°	6573.7
20°	6196.7
22.5°	5835.6
25°	5430.1
27.5°	4901.0
30°	4254.7
32.5°	3472.2
35°	2648.5
37.5°	1894.5
40°	1235.5
42.5°	738.2
45°	424.5
47.5°	237.6
50°	117.2
52.5°	53.9
55°	12.6
57.5°	3.2
60°	6.4
62.5°	9.5
65°	0.0
67.5°	6.4
70°	3.2
72.5°	3.2
75°	9.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	3.2
87.5°	0.0
90°	0.0

(END OF REPORT)