

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247726

Luminaire Tested: **LD8B80D010 ER8B80835 8LBS0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-88)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80835 8LBS0MW
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9265.0 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247726

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBS0MW

Luminous Intensity Polar Plot





TEST NUMBER: P247726

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBS0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		86	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73		80	76	72		78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71	67	63	61
5	83	72	64	59	81	71	64	58	69	62	58		67	61	57		65	60	57	55
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	47		57	51	46		55	50	46	44
8	67	55	48	43	66	55	47	42	53	47	42		52	46	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48	42	38	37
10	60	47	40	36	58	47	40	35	46	40	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151708
5°	151328
10°	150197
15°	148632
20°	145890
25°	142656
30°	137866
35°	131600
40°	122891
45°	105268
50°	79150
55°	53654
60°	34907
65°	25611
70°	20917
75°	23709
80°	24861
85°	20167



TEST NUMBER: P247726

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBS0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	463.9	5.0
10°-20°	1309.7	14.1
20°-30°	1926.8	20.8
30°-40°	2176.4	23.5
40°-50°	1832.9	19.8
50°-60°	924.8	10.0
60°-70°	362.3	3.9
70°-80°	204.6	2.2
80°-90°	63.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3700.5	39.9
0°-40°	5876.9	63.4
0°-60°	8634.5	93.2
0°-90°	9265.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9265.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4920	
5°	4889	464
15°	4656	1310
25°	4193	1927
35°	3496	2176
45°	2414	1833
55°	998	925
65°	351	362
75°	199	205
85°	57	64
90°	0	



TEST NUMBER: P247726

CATALOG NUMBER: LD8B80D010 ER8B80835 8LBS0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4919.8
2.5°	4914.8
5°	4888.8
7.5°	4854.8
10°	4796.8
12.5°	4724.8
15°	4655.8
17.5°	4550.8
20°	4445.8
22.5°	4331.8
25°	4192.8
27.5°	4035.8
30°	3871.9
32.5°	3687.9
35°	3495.9
37.5°	3275.9
40°	3052.9
42.5°	2748.9
45°	2413.9
47.5°	2029.9
50°	1649.9
52.5°	1307.0
55°	998.0
57.5°	752.0
60°	566.0
62.5°	432.0
65°	351.0
67.5°	286.0
70°	232.0
72.5°	224.0
75°	199.0
77.5°	166.0
80°	140.0
82.5°	89.0
85°	57.0
87.5°	18.0
90°	0.0

(END OF REPORT)