

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250484

Luminaire Tested: **LD8B80D010 ER8B80850 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250484
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80850 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7419.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250484

CATALOG NUMBER: LD8B80D010 ER8B80850 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250484

CATALOG NUMBER: LD8B80D010 ER8B80850 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290145
5°	282809
10°	253524
15°	225799
20°	205985
25°	187150
30°	153461
35°	100996
40°	50382
45°	18752
50°	5694
55°	688
60°	395
65°	0
70°	289
75°	1156
80°	0
85°	1132



TEST NUMBER: P250484

CATALOG NUMBER: LD8B80D010 ER8B80850 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	837.7	11.3
10°-20°	1991.7	26.8
20°-30°	2481.3	33.4
30°-40°	1673.7	22.6
40°-50°	395.8	5.3
50°-60°	28.9	0.4
60°-70°	5.2	0.1
70°-80°	3.8	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5310.7	71.6
0°-40°	6984.5	94.1
0°-60°	7409.2	99.9
0°-90°	7419.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7419.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9409	
5°	9136	838
15°	7073	1992
25°	5500	2481
35°	2683	1674
45°	430	396
55°	13	29
65°	0	5
75°	10	4
85°	3	1
90°	0	



TEST NUMBER: P250484

CATALOG NUMBER: LD8B80D010 ER8B80850 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9409.2
2.5°	9393.2
5°	9136.4
7.5°	8671.1
10°	8096.7
12.5°	7554.4
15°	7073.0
17.5°	6659.0
20°	6277.1
22.5°	5911.3
25°	5500.5
27.5°	4964.6
30°	4309.9
32.5°	3517.3
35°	2682.9
37.5°	1919.1
40°	1251.6
42.5°	747.8
45°	430.0
47.5°	240.7
50°	118.7
52.5°	54.6
55°	12.8
57.5°	3.2
60°	6.4
62.5°	9.7
65°	0.0
67.5°	6.4
70°	3.2
72.5°	3.2
75°	9.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	3.2
87.5°	0.0
90°	0.0

(END OF REPORT)