

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250358

Luminaire Tested: **LD8B80D010 ER8B80927 8LBN0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250358  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B80D010 ER8B80927 8LBN0GPH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5314.5 lumens  
Efficiency: N/A  
Efficacy: 71.4 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250358

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBN0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250358

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBN0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  | 0   |     |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 |  | 101 | 100 | 99  |  | 98  | 97  | 96  | 94  |
| 2   | 109 | 104 | 101 | 97  | 107 | 103 | 99  | 96  | 99  | 97  | 94  |  | 96  | 94  | 92  |  | 94  | 92  | 90  | 89  |
| 3   | 104 | 98  | 93  | 90  | 102 | 97  | 92  | 89  | 94  | 90  | 88  |  | 92  | 89  | 86  |  | 89  | 87  | 85  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 83  | 89  | 85  | 82  |  | 87  | 84  | 81  |  | 85  | 82  | 80  | 78  |
| 5   | 95  | 87  | 82  | 78  | 93  | 86  | 81  | 77  | 84  | 80  | 77  |  | 83  | 79  | 76  |  | 81  | 78  | 75  | 74  |
| 6   | 90  | 82  | 77  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  |  | 79  | 75  | 71  |  | 77  | 74  | 71  | 70  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 67  |  | 74  | 70  | 67  | 66  |
| 8   | 83  | 74  | 68  | 64  | 81  | 73  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 70  | 66  | 63  | 62  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 64  | 61  | 69  | 64  | 61  |  | 68  | 63  | 60  |  | 67  | 63  | 60  | 59  |
| 10  | 76  | 67  | 61  | 58  | 75  | 66  | 61  | 58  | 65  | 61  | 57  |  | 65  | 60  | 57  |  | 64  | 60  | 57  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250358

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBN0GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 762.3  | 14.3      |
| 10°-20°   | 1656.9 | 31.2      |
| 20°-30°   | 1778.8 | 33.5      |
| 30°-40°   | 961.4  | 18.1      |
| 40°-50°   | 150.0  | 2.8       |
| 50°-60°   | 4.1    | 0.1       |
| 60°-70°   | 1.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 4198.0 | 79.0      |
| 0°-40°    | 5159.4 | 97.1      |
| 0°-60°    | 5313.5 | 100.0     |
| 0°-90°    | 5314.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5314.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 8492 |      |
| 5°  | 8325 | 762  |
| 15° | 5916 | 1657 |
| 25° | 3943 | 1779 |
| 35° | 1510 | 961  |
| 45° | 138  | 150  |
| 55° | 0    | 4    |
| 65° | 0    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P250358

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBN0GPH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 8492.1 |
| 1°    | 8508.2 |
| 2°    | 8500.2 |
| 3°    | 8471.0 |
| 4°    | 8415.1 |
| 5°    | 8324.6 |
| 6°    | 8199.9 |
| 7°    | 8032.0 |
| 8°    | 7822.1 |
| 9°    | 7580.4 |
| 10°   | 7311.6 |
| 11°   | 7029.8 |
| 12°   | 6737.3 |
| 13°   | 6445.1 |
| 14°   | 6173.7 |
| 15°   | 5915.8 |
| 16°   | 5679.1 |
| 17°   | 5450.5 |
| 18°   | 5237.8 |
| 19°   | 5038.5 |
| 20°   | 4847.0 |
| 21°   | 4660.8 |
| 22°   | 4485.2 |
| 23°   | 4310.0 |
| 24°   | 4126.5 |
| 25°   | 3942.9 |
| 26°   | 3756.7 |
| 27°   | 3544.2 |
| 28°   | 3310.1 |
| 29°   | 3071.1 |
| 30°   | 2821.0 |
| 31°   | 2552.5 |
| 32°   | 2283.8 |
| 33°   | 2018.0 |
| 34°   | 1749.5 |
| 35°   | 1510.1 |
| 37.5° | 965.1  |
| 40°   | 558.3  |
| 42.5° | 297.9  |
| 45°   | 138.4  |
| 47.5° | 74.6   |
| 50°   | 24.1   |
| 52.5° | 2.7    |
| 55°   | 0.0    |
| 57.5° | 2.7    |



TEST NUMBER: P250358

CATALOG NUMBER: LD8B80D010 ER8B80927 8LBN0GPH

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 60°   | 2.7 |
| 62.5° | 0.0 |
| 65°   | 0.0 |
| 67.5° | 2.7 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)