

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249861

Luminaire Tested: **LD8B80D010 ER8B80930 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80930 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6225.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	778.6	12.5
10°-20°	1827.8	29.4
20°-30°	1997.7	32.1
30°-40°	1188.8	19.1
40°-50°	326.1	5.2
50°-60°	73.9	1.2
60°-70°	22.8	0.4
70°-80°	7.0	0.1
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4604.1	74.0
0°-40°	5792.9	93.1
0°-60°	6192.9	99.5
0°-90°	6225.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6225.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8538	
5°	8401	779
15°	6560	1828
25°	4413	1998
35°	1881	1189
45°	381	326
55°	74	74
65°	23	23
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	8537.9
1°	8554.7
2°	8544.1
3°	8523.1
4°	8474.6
5°	8401.0
6°	8306.2
7°	8179.7
8°	8032.3
9°	7861.7
10°	7670.0
11°	7465.6
12°	7246.6
13°	7021.2
14°	6787.3
15°	6559.9
16°	6336.6
17°	6117.4
18°	5898.4
19°	5679.3
20°	5466.6
22.5°	4931.5
25°	4413.3
27.5°	3842.3
30°	3208.3
32.5°	2527.9
35°	1881.2
37.5°	1308.2
40°	867.9
42.5°	568.8
45°	381.3
47.5°	252.8
50°	168.5
52.5°	103.2
55°	73.8
57.5°	52.7
60°	40.0
62.5°	29.5
65°	23.2
67.5°	14.8
70°	10.5
72.5°	8.4
75°	6.3
77.5°	4.3
80°	4.3



TEST NUMBER: P249861

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	2.1
85°	2.1
87.5°	2.1
90°	0.0

(END OF REPORT)