

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250029

Luminaire Tested: **LD8B80D010 ER8B80930 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250029  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13951)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B80D010 ER8B80930 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6089.3 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250029

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P250029

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	58		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250029

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	805.0	13.2
10°-20°	1846.9	30.3
20°-30°	1962.1	32.2
30°-40°	1119.5	18.4
40°-50°	277.6	4.6
50°-60°	54.6	0.9
60°-70°	16.5	0.3
70°-80°	3.9	0.1
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4614.1	75.8
0°-40°	5733.6	94.2
0°-60°	6065.7	99.6
0°-90°	6089.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6089.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8869	
5°	8712	805
15°	6635	1847
25°	4332	1962
35°	1751	1120
45°	314	278
55°	51	55
65°	13	16
75°	0	4
85°	4	3
90°	0	



TEST NUMBER: P250029

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8869.1
1°	8886.2
2°	8879.8
3°	8848.1
4°	8792.9
5°	8712.3
6°	8606.5
7°	8460.2
8°	8292.7
9°	8095.7
10°	7879.5
11°	7650.6
12°	7404.8
13°	7154.7
14°	6898.3
15°	6635.4
16°	6387.5
17°	6137.5
18°	5902.2
19°	5662.7
20°	5436.0
22.5°	4874.3
25°	4331.8
27.5°	3749.1
30°	3104.7
32.5°	2413.8
35°	1750.6
37.5°	1205.9
40°	780.0
42.5°	493.8
45°	313.7
47.5°	205.6
50°	129.3
52.5°	78.5
55°	50.8
57.5°	40.2
60°	25.4
62.5°	23.3
65°	12.8
67.5°	12.8
70°	10.6
72.5°	6.4
75°	0.0
77.5°	2.1
80°	2.1



TEST NUMBER: P250029

CATALOG NUMBER: LD8B80D010 ER8B80930 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	4.3
85°	4.3
87.5°	2.1
90°	0.0

(END OF REPORT)