

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247026

Luminaire Tested: **LD8B80D010 ER8B80935 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247026
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80935 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6795.1 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247026

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247026

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96		98	95	94		95	93	92	90
3	105	100	95	92	103	98	94	91	96	92	90		93	91	88		91	89	87	85
4	101	94	90	86	99	93	89	85	91	87	84		89	86	83		87	85	83	81
5	97	90	85	81	95	89	84	80	87	83	80		85	82	79		84	81	78	77
6	93	85	80	76	91	84	80	76	83	79	76		82	78	75		80	77	75	73
7	89	81	76	72	88	81	76	72	79	75	72		78	74	72		77	74	71	70
8	86	78	72	69	85	77	72	69	76	72	69		75	71	68		74	71	68	67
9	82	74	69	66	81	74	69	66	73	69	65		72	68	65		71	68	65	64
10	79	71	66	63	79	71	66	63	70	66	63		69	65	62		69	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	532293
5°	503973
10°	379552
15°	263818
20°	196662
25°	148029
30°	98983
35°	51810
40°	20010
45°	7400
50°	1881
55°	366
60°	56
65°	190
70°	234
75°	0
80°	0
85°	318



TEST NUMBER: P247026

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1415.7	20.8
10°-20°	2341.3	34.5
20°-30°	1973.8	29.0
30°-40°	895.6	13.2
40°-50°	156.4	2.3
50°-60°	8.5	0.1
60°-70°	1.3	0.0
70°-80°	1.5	0.0
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5730.8	84.3
0°-40°	6626.5	97.5
0°-60°	6791.3	99.9
0°-90°	6795.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6795.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17262	
5°	16281	###
15°	8264	2341
25°	4351	1974
35°	1376	896
45°	170	156
55°	7	9
65°	3	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P247026

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	17261.9
2.5°	17109.3
5°	16281.3
7.5°	14477.8
10°	12121.6
12.5°	9943.8
15°	8263.9
17.5°	7001.8
20°	5993.0
22.5°	5105.3
25°	4350.7
27.5°	3583.2
30°	2779.9
32.5°	2023.5
35°	1376.3
37.5°	845.1
40°	497.1
42.5°	291.6
45°	169.7
47.5°	101.5
50°	39.2
52.5°	6.0
55°	6.8
57.5°	6.0
60°	0.9
62.5°	0.9
65°	2.6
67.5°	0.0
70°	2.6
72.5°	4.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.9
87.5°	2.6
90°	0.0

(END OF REPORT)