

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247074

Luminaire Tested: **LD8B80D010 ER8B80935 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247074  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B80D010 ER8B80935 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7603.0 lumens  
Efficiency: N/A  
Efficacy: 102.2 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247074

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247074

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	130826
5°	133378
10°	139100
15°	146959
20°	152470
25°	153575
30°	146315
35°	129059
40°	104040
45°	73865
50°	44394
55°	19999
60°	5156
65°	1109
70°	550
75°	369
80°	178
85°	0



TEST NUMBER: P247074

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	415.6	5.5
10°-20°	1301.5	17.1
20°-30°	2058.2	27.1
30°-40°	2114.9	27.8
40°-50°	1311.9	17.3
50°-60°	371.9	4.9
60°-70°	25.1	0.3
70°-80°	3.4	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3775.4	49.7
0°-40°	5890.3	77.5
0°-60°	7574.1	99.6
0°-90°	7603.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7603.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4243	
5°	4309	416
15°	4603	1301
25°	4514	2058
35°	3428	2115
45°	1694	1312
55°	372	372
65°	15	25
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P247074

CATALOG NUMBER: LD8B80D010 ER8B80935 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4242.6
2.5°	4250.8
5°	4308.9
7.5°	4377.2
10°	4442.4
12.5°	4522.9
15°	4603.4
17.5°	4649.2
20°	4646.3
22.5°	4601.4
25°	4513.7
27.5°	4354.8
30°	4109.2
32.5°	3786.1
35°	3428.4
37.5°	3023.8
40°	2584.6
42.5°	2127.9
45°	1693.8
47.5°	1290.3
50°	925.4
52.5°	622.7
55°	372.0
57.5°	191.6
60°	83.6
62.5°	33.7
65°	15.2
67.5°	9.2
70°	6.1
72.5°	4.1
75°	3.1
77.5°	2.1
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)