

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247318

Luminaire Tested: **LD8B80D010 ER8B80940 8LBM0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201734)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B80D010 ER8B80940 8LBM0WMH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7090.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.9
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247318

CATALOG NUMBER: LD8B80D010 ER8B80940 8LBM0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P247318

CATALOG NUMBER: LD8B80D010 ER8B80940 8LBM0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	54	52
10	71	61	55	51	70	60	55	51	60	54	51	59	54	51	58	54	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241171
5°	238062
10°	223186
15°	204091
20°	187887
25°	170246
30°	140967
35°	98861
40°	56259
45°	27609
50°	13619
55°	6177
60°	2929
65°	1583
70°	162
75°	214
80°	0
85°	0



TEST NUMBER: P247318

CATALOG NUMBER: LD8B80D010 ER8B80940 8LBM0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	715.7	10.1
10°-20°	1794.6	25.3
20°-30°	2265.4	32.0
30°-40°	1629.6	23.0
40°-50°	539.4	7.6
50°-60°	117.5	1.7
60°-70°	24.2	0.3
70°-80°	2.4	0.0
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4775.8	67.4
0°-40°	6405.4	90.3
0°-60°	7062.3	99.6
0°-90°	7090.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7090.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7821	
5°	7691	716
15°	6393	1795
25°	5004	2265
35°	2626	1630
45°	633	539
55°	115	117
65°	22	24
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P247318

CATALOG NUMBER: LD8B80D010 ER8B80940 8LBM0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7821.0
1°	7832.0
2°	7822.8
3°	7797.0
4°	7749.1
5°	7690.8
6°	7610.8
7°	7506.7
8°	7391.7
9°	7266.1
10°	7127.8
11°	6986.7
12°	6833.0
13°	6684.9
14°	6535.9
15°	6393.0
16°	6252.3
17°	6117.4
18°	5983.6
19°	5855.1
20°	5725.6
21°	5592.9
22°	5463.4
23°	5322.5
24°	5170.6
25°	5003.7
26°	4828.5
27°	4633.4
28°	4427.0
29°	4197.8
30°	3959.0
31°	3707.9
32°	3443.5
33°	3166.1
34°	2894.8
35°	2626.2
37.5°	1972.2
40°	1397.6
42.5°	946.8
45°	633.1
47.5°	424.8
50°	283.9
52.5°	171.4
55°	114.9
57.5°	80.0



TEST NUMBER: P247318

CATALOG NUMBER: LD8B80D010 ER8B80940 8LBM0WMH

CANDELA DISTRIBUTION (continued):

	0°
60°	47.5
62.5°	32.5
65°	21.7
67.5°	19.5
70°	1.8
72.5°	4.5
75°	1.8
77.5°	1.8
80°	0.0
82.5°	4.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)